

Proximity sensor SIEH-M12B-NS-S-L-CR

Part number: 538253

FESTO



Data sheet

Feature	Value
Conforms to standard	EN 60947-5-2
Certification	RCM compliance mark c UL us - Listed (OL)
CE marking (see declaration of conformity)	As per EU EMC directive
Rated operating distance	6 mm
Assured operating distance	4.86 mm
Reduction factors	Aluminum = 1.0 Stainless steel, 1 mm thick = 0.45 Stainless steel, 2 mm thick = 0.9 Copper = 0.85 Brass = 1.3 Steel St 37 = 1.0
Ambient temperature	-25 °C...70 °C
Switching output	NPN
Switching element function	N/O contact
Reproducibility, switching value FS	0.3 mm
Hysteresis	0.73 mm
Max. switching frequency	600 Hz
Max. output current	200 mA
Voltage drop	2 V
Inductive protective circuit	Installed Output current <100 mA and switching frequency < 10 Hz
Short-circuit protection	Pulsed
DC operating voltage range	10 V...30 V
Residual ripple	20 %
Idle current	17 mA
Reverse polarity protection	for all electrical connections
Electrical connection	3-pin M12x1 Plug
Size	M12
Type of mounting	With lock nut
Mounting type	Flush

Feature	Value
Product weight	28 g
Housing material	High-alloy steel
Switching status indication	LED yellow
Ambient temperature with flexible cable installation	-5 °C...70 °C
Degree of protection	IP67 IP69K
Resistance to sensor fitting pressure	80 bar
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Selection of additional sensor information	With increased switching distance
Electrical output	NPN
Selection of sensor version	Fully stainless steel housing