

# Compact cylinder ADN-40-80-I-P-A

Part number: 536308

**FESTO**



## Data sheet

Feature	Value
Stroke	80 mm
Piston diameter	40 mm
Piston rod thread	M8
Cushioning	Elastic cushioning rings/pads at both ends
Mounting position	Any
Conforms to standard	ISO 21287
Piston rod end	Internal thread
Position sensing	For proximity sensor
Variants	Piston rod at one end
Operating pressure	0.06 MPa...1 MPa 0.6 bar...10 bar
Mode of operation	Double-acting
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Cleanroom suitability, measured according to ISO 14644-14	Class 5 according to ISO 14644-1
Ambient temperature	-20 °C...80 °C
Impact energy in the end positions	0.7 J
Theoretical force at 6 bar, retracting	686 N
Theoretical force at 6 bar, advancing	754 N
Moving mass	108 g
Product weight	601 g
Type of mounting	Optionally: With through-hole With internal thread With accessories
Pneumatic connection	G1/8
Note on materials	RoHS-compliant
Flange screws material	Steel
Cover material	Wrought aluminum alloy, anodized
Seals material	TPE-U(PUR)

Feature	Value
Piston rod material	High-alloy steel
Material of cylinder barrel	Wrought aluminum alloy, smooth-anodized