


Proximity sensor SIEF-M18NB-PS-S-L

Part number: 538315

FESTO



Data sheet

Feature	Value
Design	Round
Conforms to standard	EN 60947-5-2
Certification	RCM compliance mark c UL us - Listed (OL)
CE marking (see declaration of conformity)	As per EU EMC directive As per EU low voltage directive As per EU RoHS directive
UKCA marking (see declaration of conformity)	To UK instructions for EMC To UK RoHS instructions To UK instructions for electrical equipment
Measuring principle	Inductive
Rated operating distance	12 mm
Assured operating distance	9.72 mm
Reduction factors	Aluminum = 1.0 Stainless steel St 18/8 = 1.0 Copper = 1.0 Brass = 1.0 Steel St 37 = 1.0
Ambient temperature	-30 °C...85 °C
Repetition accuracy	0.24 mm
Switching output	PNP
Switching element function	N/O contact
Hysteresis	0.36 mm...1.8 mm
Max. switching frequency DC	2000 Hz
Max. output current	200 mA
Voltage drop	1.8 V
Short-circuit protection	Pulsed
DC operating voltage range	10 V...30 V
Residual ripple	10 %
Idle current	15 mA
Reverse polarity protection	for all electrical connections
Electrical connection	3-pin Fixcon M12x1 Plug

Feature	Value
Size	M18
Type of mounting	With lock nut
Tightening torque	25 Nm
Mounting type	Not flush
Product weight	38 g
Housing material	Brass PBT Chrome-plated
Switching status indication	LED yellow
Degree of protection	IP67
Resistance to interference from magnetic fields	Magnetic direct and alternating fields
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
Selection of additional sensor information	with reduction factor 1 – resistance to magnetic fields
Electrical output	PNP
Selection of sensor version	Standard