


Proximity sensor SIEF-Q40S-NA-S-2L

Part number: 538342

FESTO



Data sheet

| Feature | Value |
|--|--|
| Design | Square |
| Conforms to standard | EN 60947-5-2 |
| Certification | RCM compliance mark c UL us - Listed (OL) |
| CE marking (see declaration of conformity) | As per EU EMC directive As per EU low voltage directive As per EU RoHS directive |
| UKCA marking (see declaration of conformity) | To UK instructions for EMC To UK RoHS instructions To UK instructions for electrical equipment |
| Measuring principle | Inductive |
| Rated operating distance | 35 mm |
| Assured operating distance | 28.35 mm |
| Reduction factors | Aluminum = 1.0 Stainless steel St 18/8 = 1.0 Copper = 1.0 Brass = 1.0 Steel St 37 = 1.0 |
| Ambient temperature | -30 °C...85 °C |
| Repetition accuracy | 0.7 mm |
| Switching output | NPN |
| Switching element function | Antivalent |
| Hysteresis | 1.05 mm...5.25 mm |
| Max. switching frequency DC | 250 Hz |
| Max. output current | 200 mA |
| Voltage drop | 1.8 V |
| Short-circuit protection | Pulsed |
| DC operating voltage range | 10 V...65 V |
| Residual ripple | 10 % |
| Idle current | 15 mA |
| Reverse polarity protection | for all electrical connections |
| Electrical connection | 4-pin Fixcon M12x1 Plug |

| Feature | Value |
|---|---|
| Size | 40x40x65 mm |
| Type of mounting | With through-hole |
| Mounting type | Partially flush |
| Product weight | 156 g |
| Housing material | PA PBT-reinforced |
| Ready status indication | LED green |
| Switching status indication | LED yellow |
| Degree of protection | IP67 |
| Resistance to interference from magnetic fields | Magnetic direct and alternating fields |
| Corrosion resistance class (CRC) | 0 - No corrosion stress |
| Selection of additional sensor information | with reduction factor 1 – resistance to magnetic fields |
| Electrical output | NPN |
| Selection of sensor version | Standard |