

Connecting cable NEBU-

Part number: 539052

FESTO



Data sheet

Feature	Value
Based on norm	EN 61076-2-104
Conforms to standard	Wire colors and connection numbers as per EN 60947-5-2 EN 61076-2-101 EN 61076-2-104
Explosion prevention and protection	Observe the information on the certificate Zone 2 (ATEX) Zone 22 (ATEX)
Ready status indication	LED green
Switching status indication	LED yellow For NPN N/O contacts For PNP N/O contact
Cable designation	Without label holder With 2x label holders
Product weight	22 g...835 g
Electrical connection 1, function	Field device end
Electrical connection 1, design	Round
Electrical connection 1, connection type	Socket Cable
Electrical connection 1, cable outlet	Straight Angled Angled, can be aligned in increments of 15°
Electrical connection 1, connection technology	M12x1 A-coded as per EN 61076-2-101 M8x1 A-coded as per EN 61076-2-104 Open end
Electrical connection 1, number of pins/wires	3 ...8
Electrical connection 1, occupied pins/wires	2 ...5
Electrical connection 1, type of mounting	Screw-type lock
Electrical connection 2, function	Control side
Electrical connection 2, design	Round
Electrical connection 2, connection type	Cable Plug
Electrical connection 2, cable outlet	Straight Angled
Electrical connection 2, connection technology	M12x1 A-coded as per EN 61076-2-101 M8x1 A-coded as per EN 61076-2-104 Open end

Feature	Value
Electrical connection 2, number of pins/wires	3 ...8
Electrical connection 2, occupied pins/wires	2 ...5
Electrical connection 2, type of mounting	Screw-type lock
DC operating voltage range	0 V...250 V
Operating voltage range AC	0 V...250 V
Current rating at 40° C	3 A...4 A
Surge resistance	0.8 kV...2.5 kV
Cable length	0.1 m...30 m
Cable characteristic	Basic Standard Suitable for energy chains Suitable for robot applications
Connector cable test conditions	Flexural strength: as per Festo standard Test conditions on request Energy chain > 5 million cycles, bending radius 75 mm
Cable diameter	4.5 mm...7 mm
Cable diameter tolerance	± 0.1 mm
Cable design	2 x 0.25 mm ² 3 x 0.25 mm ² 4 x 0.25 mm ² 5 x 0.25 mm ² 5 x 1 mm ²
Nominal conductor cross section	0.25 mm ² ...1 mm ²
Degree of protection	IP65 IP68 IP69K
Note on degree of protection	In mounted state
Special features	Oil-resistant
Ambient temperature	-25 °C...80 °C
Ambient temperature with flexible cable installation	-5 °C...80 °C
CE marking (see declaration of conformity)	As per EU low voltage directive As per EU RoHS directive
UKCA marking (see declaration of conformity)	To UK RoHS instructions To UK instructions for electrical equipment
LABS (PWIS) conformity	VDMA24364-B2-L
Note on materials	RoHS-compliant Halogen-free Free of phosphoric acid ester
Contamination level	3
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
Material of cable sheath	PVC TPE-U(PUR)
Color cable sheath	Gray
Housing material	TPE-U(PUR)
Housing colour	Black
Material of screw-type lock	Brass, nickel-plated
Seals material	NBR
Material of pin contacts	Copper alloy, gold-plated
Insulating sheath material	PP