

# High-force cylinder ADNH-25- -

Part number: 539691

**FESTO**



## Data sheet

Feature	Value
Stroke	5 mm...150 mm
Piston diameter	25 mm
Based on norm	ISO 21287
Cushioning	Elastic cushioning rings/pads at both ends
Mounting position	Any
Mode of operation	Double-acting
Structural design	Piston Piston rod Profile barrel
Position sensing	For proximity sensor
Variants	Extended external thread piston rod Special thread on piston rod Extended piston rod Heat-resistant seals max. 120°C Laser etched rating plate
Operating pressure	0.08 MPa...1 MPa 0.8 bar...10 bar
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-20 °C...120 °C
Theoretical force at 6 bar, retracting	247 N
Theoretical force at 6 bar, advancing	1036 N
Type of mounting	With internal thread With accessories Optionally:
Pneumatic connection	M5
Note on materials	RoHS-compliant
Cover material	Wrought aluminum alloy Anodized
Seals material	TPE-U(PU)
Housing material	Wrought aluminum alloy Anodized

Feature	Value
Piston rod material	High-alloy steel