


Pressure sensor SDE3-D10D-B-FQ4-2P-M8

Part number: 540210

FESTO



Data sheet

Feature	Value
Certification	RCM compliance mark
CE marking (see declaration of conformity)	As per EU EMC directive As per EU RoHS directive
UKCA marking (see declaration of conformity)	To UK instructions for EMC To UK RoHS instructions
Note on materials	RoHS-compliant
Measured variable	2 x relative pressure
Method of measurement	Piezoresistive pressure sensor with display
Pressure measuring range initial value	0 MPa 0 bar 0 psi
Pressure measuring range end value	1 MPa 10 bar 145 psi
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible
Temperature of medium	0 °C...50 °C
Ambient temperature	0 °C...50 °C
Accuracy in ± % FS	2 %FS
Switching output	2xPNP
Switching function	Freely programmable
Switching element function	Switchable
Reproducibility of switching value	0.3 %
Max. output current	100 mA
Short-circuit protection	Pulsed
DC operating voltage range	15 V...30 V
Reverse polarity protection	for all electrical connections
Electrical connection 1, connection type	Plug
Electrical connection 1, connection technology	M8x1 A-coded as per EN 61076-2-104
Electrical connection 1, number of pins/wires	4
Electrical connection 1, type of mounting	Screw-type lock
Cable length	0.3 m
Type of mounting	Front panel mounting

Feature	Value
Mounting position	Any
Pneumatic connection	QS-4
Product weight	61 g
Housing material	PA-reinforced PC
Display type	Illuminated LCD
Switching status indication	LCD yellow
Setting options	Teach-in
Protection against tampering	PIN code
Setting range threshold value	0 %...100 %
Setting range hysteresis	0 %...90 %
Degree of protection	IP65
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Cleanroom class	Class 4 according to ISO 14644-1