

Compact air cylinder AEN-40- -

Part number: 536419

FESTO



Data sheet

Feature	Value
Stroke	1 mm...25 mm
Piston diameter	40 mm
Cushioning	Elastic cushioning rings/pads at both ends
Mounting position	Any
Conforms to standard	ISO 21287
Structural design	Piston Piston rod Profile barrel
Position sensing	For proximity sensor
Variants	Improved running performance Extended external thread piston rod Special thread on piston rod Extended piston rod With anti-twist protection Heat-resistant seals max. 120°C Laser etched rating plate Pulling Piston rod at one end
Operating pressure	0.1 MPa...1 MPa 1 bar...10 bar
Mode of operation	Pushing Single-acting Pulling
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-20 °C...120 °C
Theoretical force at 6 bar, retracting	606 N
Theoretical force at 6 bar, advancing	676 N
Weight surcharge per 10 mm piston rod extension	9 g
Weight surcharge per 10 mm piston rod thread extension	6 g
Type of mounting	With through-hole With internal thread With accessories Optionally:

Feature	Value
Pneumatic connection	G1/8
Note on materials	RoHS-compliant
Flange screws material	Steel
Cover material	Wrought aluminum alloy, anodized
Piston rod material	High-alloy steel
Material of cylinder barrel	Wrought aluminum alloy, smooth-anodized