


# Air preparation combination unit MSB6N-1/2:H1N3M1-WP

Part number: 541467

**FESTO**



## Data sheet

Feature	Value
Size	6
Series	MS
Actuator lock	Rotary knob with detent can be closed with accessories
Mounting position	Vertical +/- 5°
Grade of filtration	40 µm
Condensate drain	Fully automatic
Structural design	Pressure regulator with pressure gauge Standard filter Standard oil mist lubricator
Bowl guard	Plastic bowl guard
Pressure gauge	with pressure gauge
Operating pressure	2 bar...12 bar
Pressure regulation range	1 bar...12 bar
Standard nominal flow rate	3500 l/min
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:-] Inert gas
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Storage temperature	-10 °C...60 °C
For use in the food industry	See supplementary material information
Air quality class at the output	Compressed air as per ISO 8573-1:2010 [7:4:-]
Product weight	2000 g
Type of mounting	With accessories
Pneumatic connection 1	1/2 NPT
Pneumatic connection 2	1/2 NPT
Note on materials	RoHS-compliant
Housing material	Die-cast aluminum
Material of bowl	PC