

Shut off valve MS6-EE-3/8-10V24-S

Part number: 542606

FESTO



Data sheet

| Feature | Value |
|--|--|
| Structural design | Piston gate valve |
| Actuation type | Electrical |
| Exhaust air function | Without flow control option |
| Manual override | Non-detenting |
| Reset method | Mechanical spring |
| Type of control | Pilot-controlled |
| Valve function | 3/2, closed, monostable |
| Operating pressure | 4 bar...10 bar |
| C value | 22 l/sbar |
| b-value | 0.5 |
| Standard nominal flow rate | 5500 l/min |
| Duty cycle | 100% |
| Coil characteristics | 24 V DC: 2.5 W |
| Permissible voltage fluctuations | +/- 10 % |
| Operating medium | Compressed air as per ISO 8573-1:2010 [7:4:4] Inert gas |
| Information on operating and pilot media | Operation with oil lubrication possible (required for further use) |
| Corrosion resistance class (CRC) | 2 - Moderate corrosion stress |
| Note on materials | RoHS-compliant |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Temperature of medium | -10 °C...60 °C |
| Degree of protection | IP65 |
| Ambient temperature | -10 °C...50 °C |
| For use in the food industry | See supplementary material information |
| Type of mounting | Line installation With accessories Optionally: |
| Mounting position | Any |
| Flow direction | Non-reversible |
| Product weight | 816 g |
| Pneumatic connection 1 | G3/8 |
| Pneumatic connection 2 | G3/8 |

| Feature | Value |
|------------------------|--|
| Pneumatic connection 3 | G1/2 |
| Pilot air supply port | Internal |
| Electrical connection | Form C Plug as per DIN EN 175301-803 Rectangular design |
| Seals material | NBR |
| Housing material | Die-cast aluminum |