

# Mini slide DGSL-25-200-P1A

Part number: 544047

FESTO



## Data sheet

Feature	Value
Stroke	200 mm
Adjustable end-position range/front length	110 mm
Adjustable end-position range/rear length	49 mm
Piston diameter	32 mm
Drive unit operating mode	Yoke
Cushioning	Elastic cushioning rings/pads at both ends with fixed stop
Mounting position	Any
Guide	Ball bearing cage guide
Structural design	Yoke Piston Piston rod Slide
Position sensing	For proximity sensor
Operating pressure	0.1 MPa...0.8 MPa 1 bar...8 bar
Max. speed	0.8 m/s
Repetition accuracy	±0.01 mm
Mode of operation	Double-acting
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	0 - No corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Cleanroom class	Class 7 according to ISO 14644-1
Ambient temperature	0 °C...60 °C
Impact energy in the end positions	0.25 Nm
Cushioning length	4.8 mm
Max. force F <sub>y</sub>	4800 N
Max. force F <sub>z</sub>	4800 N
Max. torque M <sub>x</sub>	130 Nm
Max. torque M <sub>y</sub>	80 Nm
Max. torque M <sub>z</sub>	80 Nm
Theoretical force at 6 bar, retracting	415 N

Feature	Value
Theoretical force at 6 bar, advancing	483 N
Moving mass	2432 g
Product weight	6347 g
Alternative connections	See product drawing
Type of mounting	With through-hole
Pneumatic connection	G1/8
Note on materials	RoHS-compliant
Cover material	Wrought aluminum alloy
Seals material	HNBR
Housing material	Wrought aluminum alloy
Piston rod material	High-alloy stainless steel