

# Valve manifold VTSA-F-FB-NPT

Part number: 547966

**FESTO**



## Data sheet

Feature	Value
Electrical actuation	Ethernet Fieldbus Integrated controller
Electrical I/O system	yes
Valve terminal type	45
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Ambient temperature	-5 °C...50 °C
Storage temperature	-20 °C...60 °C
Relative air humidity	0 - 90 %
Degree of protection	IP65 NEMA 4
Corrosion resistance class (CRC)	0 - No corrosion stress
Operating pressure	-0.09 MPa...1 MPa -0.9 bar...10 bar
Pilot pressure MPa	0.3 MPa...1 MPa
Pilot pressure	3 bar...10 bar
Operating pressure for valve manifold with internal pilot air supply	0.3 MPa...1 MPa 3 bar...10 bar
LABS (PWIS) conformity	VDMA24364-B1/B2-L
CE marking (see declaration of conformity)	As per EU EMC directive
UKCA marking (see declaration of conformity)	To UK instructions for EMC To UK RoHS instructions
KC characters	KC EMC
Certification	BIA C-Tick c UL us - Recognized (OL)
Note on materials	RoHS-compliant
Valve manifold design	Modular, pneumatic valve sizes can be mixed
Max. no. of valve positions	32
Max. no. of pressure zones	16
Actuation type	Electrical

Feature	Value
Valve function	2x2/2 closed, monostable 2x3/2, closed, monostable 2x3/2, open, monostable 2x3/2, open/closed, monostable 5/2, bistable 5/2, bistable, dominant 5/2, monostable 5/2, monostable, safety function 5/3, pressurized 5/3, exhausted 5/3, closed 5/3, connection 2 pressurized, 4 exhausted
Structural design	Piston gate valve
Valve size	18 mm 26 mm 42 mm 52 mm 65 mm
Pilot air supply port	External Internal
Max. standard nominal flow rate	700 l/min at 18 mm 1350 l/min at 26 mm 1860 l/min at 42 mm 2900 l/min at 52 mm 4000 l/min at 65 mm
Suitability for vacuum	yes
Exhaust air function	Via throttle plate
Pneumatic working port	1/8 NPT 1/4 NPT 3/8 NPT 1/2 NPT QS-5/16 QS-3/8 QS-1/2
Signal status display	LED
Nominal operating voltage DC	24 V
Permissible voltage fluctuations	+/- 10 %