


Air solenoid valve VZWM-L-M22C-N34-F5-R1

Part number: 546173

FESTO



Data sheet

Feature	Value
Structural design	Diaphragm valve servo-controlled
Actuation type	Electrical
Sealing principle	Soft
Mounting position	Preferably upright
Type of mounting	Line installation
Fitting connection	3/4 NPT
Electrical connection	Solenoid coil type MH-... , coil can be ordered as an accessory
Nominal width	25 mm
Valve function	2/2, closed, monostable
Flow direction	Non-reversible
Medium	Compressed air as per ISO 8573-1:2010 [7:4:4] Inert gas Water Neutral liquids
Medium pressure of liquid media	0.5 bar...6 bar
Medium pressure of gaseous media	0.5 bar...10 bar
Differential pressure	0.5 bar
Type of control	Pilot-controlled
Max. viscosity	22 mm ² /s
Temperature of medium	-10 °C...60 °C
Temperature of liquid media	5 °C...50 °C
Ambient temperature	-10 °C...60 °C
Flow rate Kv	8,5 m ³ /h
Standard nominal flow rate	10000 l/min
On switching time	15 ms
Response time "on" for liquid media	420 ms

Feature	Value
Switching time off	12 ms
Response time "off" for liquid media	950 ms
b-value	0.5
C value	39 l/sbar
Note on materials	RoHS-compliant
LABS (PWIS) conformity	VDMA24364 zone III
Housing material	Cast stainless steel
Material number of housing	1.4581
Seals material	NBR
Armature tube material	High-alloy steel
Product weight	1200 g
CE marking (see declaration of conformity)	as per EU pressure equipment directive
UKCA marking (see declaration of conformity)	according to UK regulations for pressure equipment
Corrosion resistance class (CRC)	3 - High corrosion stress
Max. torque for cover screw	30 Nm
Max. tightening torque for connecting thread	200 Nm
Max. tightening torque for coil fastening	2 Nm