


Round cylinder DSNU-1 5/8"-P-A-S2

Part number: 548517

FESTO



Data sheet

Feature	Value
Stroke	0.4 in...20 in
Piston diameter	1 5/8"
Piston rod thread	1/2-20 UNF-2A
Based on norm	ISO 6431
Cushioning	Elastic cushioning rings/pads at both ends
Mounting position	Any
Piston rod end	External thread
Structural design	Piston Piston rod
Position sensing	For proximity sensor
Variants	Through piston rod
Operating pressure	0.1 MPa...1 MPa 1 bar...10 bar
Mode of operation	Double-acting
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-4 °F...176 °F
Impact energy in the end positions	0.516 ft-lbf
Theoretical force at 6 bar, retracting	127 lbf
Theoretical force at 6 bar, advancing	151 lbf
Moving mass at 0 mm stroke	8.11 oz
Additional weight per 10 mm stroke	0.564 oz
Type of mounting	With accessories
Pneumatic connection	1/4 NPT
Note on materials	RoHS-compliant
Cover material	Wrought aluminum alloy
Seals material	NBR TPE-U(PU)
Piston rod material	High-alloy stainless steel
Material of cylinder barrel	High-alloy stainless steel