


Electrical interface VMPA-ASI-EPL-E-4E4A-Z

Part number: 546988

FESTO



Data sheet

| Feature | Value |
|---|--|
| Dimensions W x L x H | 85 mm x 122.9 mm x 55.1 mm |
| Fieldbus interface | Socket, M12 (AS-i Out) Plug, M12 (AS-i In) |
| Device-specific diagnostics | AS-i voltage AS-i address Watchdog/I/O status Additional supply missing or undervoltage |
| Max. no. of valve positions | 4 |
| Response delay inputs | Typ. 3 ms at 24 V |
| Number of slaves per device | 1 |
| Operating voltage range DC electronics/sensors | US+ / US- : <= AS-interface bus voltage - 2.5V |
| AS-Interface DC operating voltage range | 26.5 V...31.6 V |
| DC load voltage operating voltage range | 21.6 V...26.4 V |
| Information concerning load voltage | Via load voltage connection (24 V DC) |
| Logic level digital inputs | ON: 11 - 30V OFF: -30 - 5V |
| Max. number of inputs | 4 |
| AS interface residual ripple | <= 20 mVss |
| Load voltage residual ripple | 4 Vss |
| Current consumption with load voltage from AS-Interface and load voltage connection | Max. total current at inputs 350 mA Max. total current at outputs MPA12: 270 mA Max. total current at outputs MPA2: 533 mA |
| Corrosion resistance class (CRC) | 1 - Low corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Storage temperature | -20 °C...40 °C |
| Degree of protection | IP20 |
| Ambient temperature | -5 °C...50 °C |
| Product weight | 360 g |
| Input characteristics | As per IEC 1131-2, type 02 |
| Input switching logic | PNP (positive switching) |
| Addressing range | 1 ... 31 |
| LED display (bus-specific) | AS-i: AS-Interface mode Aux/Pwr: AS-Interface power supply Fault: AS interface fault |

| Feature | Value |
|--------------------------------|---|
| LED display (product-specific) | Signal at input/output |
| Product identification | ID code: ID=Fh, ID1=Fh, ID2=Eh IO code: 7h Profile: S-7.F.E |
| Type of mounting | With through-hole With H-rail Optionally: |
| Housing material | Die-cast aluminum PA |
| Note on materials | RoHS-compliant |