

ISO cylinder CRDSNU-25-

Part number: 552790

FESTO



Data sheet

Feature	Value
Stroke	1 mm...500 mm
Piston diameter	25 mm
Piston rod thread	M6 M10x1.25
Based on norm	ISO 6432
Cushioning	Elastic cushioning rings/pads at both ends Self-adjusting pneumatic end-position cushioning Pneumatic cushioning, adjustable at both ends
Mounting position	Any
Piston rod end	External thread Internal thread
Structural design	Piston Piston rod Cylinder barrel
Position sensing	For proximity sensor
Variants	Hard scraper For unlubricated operation Increased chemical resistance Extended external thread piston rod Extended piston rod Bearing cover without mounting thread Lateral supply port Through piston rod Heat-resistant seals max. 120°C Temperature range -40 to 80°C Piston rod at one end
Operating pressure	0.1 MPa...1 MPa 1 bar...10 bar
Mode of operation	Double-acting
CE marking (see declaration of conformity)	as per EU explosion protection directive (ATEX)
UKCA marking (see declaration of conformity)	acc. to UK EX instructions
Explosion protection certification outside the EU	EPL Db (GB) EPL Gb (GB)

Feature	Value
Explosion prevention and protection	Zone 1 (ATEX) Zone 1 (UKEX) Zone 2 (ATEX) Zone 21 (ATEX) Zone 21 (UKEX) Zone 22 (ATEX)
ATEX category gas	II 2G
ATEX category for dust	II 2D
Type of ignition protection for gas	Ex h IIC T4 Gb
Type of (ignition) protection for dust	Ex h IIIC T120°C Db
Explosive ambient temperature	-20°C ≤ Ta ≤ +60°C
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	3 - High corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L VDMA24364 zone III
Cleanroom class	Class 6 according to ISO 14644-1
For use in the food industry	See declaration of conformity
Ambient temperature	-40 °C...120 °C
Theoretical force at 6 bar, retracting	247 N
Theoretical force at 6 bar, advancing	295 N
Moving mass at 0 mm stroke	73 g
Additional moving mass per 10 mm stroke	6 g
Basic weight with 0 mm stroke	410 g
Additional weight per 10 mm stroke	11 g
Type of mounting	With accessories
Pneumatic connection	G1/8
Note on materials	RoHS-compliant
Cover material	High-alloy stainless steel
Piston rod material	High-alloy stainless steel
Material of cylinder barrel	High-alloy stainless steel