



Diffuse scan

SOEG-RT-M18-PA-K-2L

Part number: 547912

FESTO



Data sheet

Feature	Value
Design	Round
Conforms to standard	EN 60947-5-2
Certification	RCM compliance mark c UL us - Listed (OL)
CE marking (see declaration of conformity)	As per EU EMC directive As per EU RoHS directive
UKCA marking (see declaration of conformity)	To UK instructions for EMC To UK RoHS instructions
Measured variable	Position
Measuring principle	Optoelectronic
Method of measurement	Reflection light sensor
Type of light	Red
Working range	40 mm...600 mm
Ambient temperature	-25 °C...55 °C
Switching output	PNP
Switching element function	Antivalent
Hysteresis	60 mm
Max. switching frequency	1000 Hz
Max. output current	200 mA
Voltage drop	2 V
Short-circuit protection	Pulsed
DC operating voltage range	10 V...36 V
Residual ripple	20 %
Idle current	20 mA
Reverse polarity protection	for all electrical connections
Electrical connection	4-wire Cable
Cable length	2.5 m
Material of cable sheath	TPE-U(PUR)
Insulating sheath material	PVC
Size	M18
Type of mounting	With lock nut

Feature	Value
Tightening torque	20 Nm
Mounting position	Any
Product weight	121 g
Housing material	Brass Chrome-plated
Switching status indication	LED yellow
Function reserve indication	LED green
Setting options	Potentiometer
Setting range, lower limit	40 mm
Setting range, upper limit	600 mm
Ambient temperature with flexible cable installation	-5 °C...55 °C
Degree of protection	IP65 IP67
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364 zone III