


Compact air cylinder ADN-20- -EL-

Part number: 548214

FESTO



Data sheet

Feature	Value
Stroke	10 mm...300 mm
Piston diameter	20 mm
Piston rod thread	M8
Based on norm	ISO 21287
Cushioning	Elastic cushioning rings/pads at both ends
Mounting position	Any
Piston rod end	Internal thread
Structural design	Piston Piston rod Cylinder barrel
Position sensing	For proximity sensor
Variants	With end-position locking at both ends With rear end-position locking With front end-position locking Extended external thread piston rod Special thread on piston rod Extended piston rod Laser etched rating plate
Operating pressure	0.25 MPa...1 MPa 2.5 bar...10 bar
Mode of operation	Double-acting
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-20 °C...80 °C
Impact energy in the end positions	0.2 J
Theoretical force at 6 bar, retracting	141 N
Theoretical force at 6 bar, advancing	188 N
Additional moving mass per 10 mm stroke	6 g
Type of mounting	With internal thread With accessories
Pneumatic connection	M5
Note on materials	RoHS-compliant

Feature	Value
Cover material	Wrought aluminum alloy Anodized
Piston rod material	High-alloy steel
Material of cylinder barrel	Wrought aluminum alloy Smooth anodized