

Micro filter MS9-LFM-1-AUM

Part number: 553000

FESTO



Data sheet

Feature	Value
Series	MS
Size	9
Structural design	Fiber filter
Grade of filtration	0.01 µm
Condensate drain	Manually rotating
Operating pressure	0 MPa...2 MPa 0 bar...20 bar
Operating medium	Compressed air as per ISO 8573-1:2010 [6:::4]
Air quality class at the output	Compressed air as per ISO 8573-1:2010 [3:::2]
Max. standard flow rate for air quality class	6500 l/min
Min. standard flow rate for air quality class	325 l/min
Filter efficiency	99.9999 %
Max. condensate volume	225 ml
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Temperature of medium	-10 °C...60 °C
Ambient temperature	-10 °C...60 °C
Storage temperature	-10 °C...60 °C
Filter efficiency, fine particles	99.995 %
MPPS	0.08 µm
MPPS filter efficiency	99.981 %
Residual oil content	0.01 mg/m³
Filter efficiency, oil aerosol	99 %
Type of mounting	Line installation With accessories Optionally:
Mounting position	Vertical +/- 5°
Pneumatic connection 1	G1
Pneumatic connection 2	G1
Housing material	Die-cast aluminum
Covering material	PA
Compressed air filter material	Borosilicate fiber

Feature	Value
Material of bowl	Wrought aluminum alloy
Inspection window material	PA
Seals material	NBR
Product weight	2000 g