


Swivel actuator unit DSL-25-80-270-P-A-S2-B

Part number: 556480

FESTO



Data sheet

Feature	Value
Adjustment range of swivel angle	0 deg...270 deg
Stroke	80 mm
Piston diameter	25 mm
Swivel angle	0 deg...272 deg
Cushioning	Elastic cushioning rings/pads at both ends
Mounting position	Any
Precision adjustment	-6 deg
Mode of operation	Double-acting
Structural design	Rotary vane
Position sensing	For proximity sensor
Variants	Through piston rod
Protection against torsion/guide	With plain-bearing guide
Operating pressure	2.5 bar...8 bar
Max. impact velocity	500 mm/s
Max. swivel frequency at 6 bar	2 Hz
Swivel angle backlash	2 deg
Repetition accuracy	1 deg
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	-10 °C...60 °C
Dynamic load torque	0.45 Nm
Theoretical force at 6 bar, retracting	173.5 N
Theoretical force at 6 bar, advancing	246 N
Theoretical torque at 6 bar	5 Nm
Permissible mass moment of inertia	0.00011 kgm ²
Product weight	1500 g
Basic weight with 0 mm stroke	1500 g
Additional weight per 10 mm stroke	67 g

Feature	Value
Type of mounting	Clamped in T slot With external thread Optionally:
Pneumatic connection	M5
Cover material	Wrought aluminum alloy Anodized
Seals material	TPE-U(PU)
Housing material	Wrought aluminum alloy Smooth anodized
Piston rod material	Tempered steel