


# Compact air cylinder ADNGF-16-15-P-A

Part number: 554214

**FESTO**



## Data sheet

| Feature                                  | Value  |
|--|--|
| Stroke                                   | 15 mm  |
| Piston diameter                          | 16 mm  |
| Based on norm                            | ISO 21287  |
| Cushioning                               | Elastic cushioning rings/pads at both ends                         |
| Mounting position                        | Any  |
| Structural design                        | Piston<br>Piston rod<br>Profile barrel                             |
| Position sensing                         | For proximity sensor   |
| Protection against torsion/guide         | Guide rod with yoke  |
| Operating pressure                       | 0.15 MPa...1 MPa<br>1.5 bar...10 bar                               |
| Mode of operation                        | Double-acting  |
| Operating medium                         | Compressed air as per ISO 8573-1:2010 [7:4:4]                      |
| Information on operating and pilot media | Operation with oil lubrication possible (required for further use) |
| Corrosion resistance class (CRC)         | 2 - Moderate corrosion stress                                      |
| LABS (PWIS) conformity                   | VDMA24364-B1/B2-L  |
| Ambient temperature                      | -20 °C...80 °C   |
| Impact energy in the end positions       | 0.15 J   |
| Theoretical force at 6 bar, retracting   | 90 N   |
| Theoretical force at 6 bar, advancing    | 121 N  |
| Moving mass                              | 65 g   |
| Product weight                           | 112 g  |
| Pneumatic connection                     | M5   |
| Note on materials                        | RoHS-compliant   |
| Flange screws material                   | Steel  |
| Cover material                           | Wrought aluminum alloy, anodized                                   |
| Seals material                           | TPE-U(PUR)   |
| End plate material                       | Wrought aluminum alloy, anodized                                   |
| Piston rod material                      | High-alloy steel   |
| Material of cylinder barrel              | Wrought aluminum alloy, smooth-anodized                            |