


Drive shaft adapter EAMB-16-7-8X15-8X10

Part number: 558034

FESTO



Data sheet

Feature	Value
Diameter of holder 1	8 mm
Diameter of holder 2	8 mm
Size	50
Nominal length	15 mm
Mounting position	Any
Max. rotational speed	10000 rpm
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-25 °C...60 °C
Relative air humidity	0 - 95 %
Ambient temperature	-25 °C...60 °C
Mass moment of inertia	0.45 kgmm ²
Transferable torque	4.5 Nm
Product weight	20.2 g
Note on materials	RoHS-compliant