


Motor flange
EAMF-A-38B-40A
Part number: 558175



Data sheet

Feature	Value
Mounting position	Any
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-25 °C...60 °C
Relative air humidity	0 - 95 %
Ambient temperature	-10 °C...60 °C
Product weight	43 g
Interface code, motor in	40A
Interface code, coupling housing	38B
Note on materials	RoHS-compliant