

# Plastic tubing PUN-V0-10X2-BL-C

Part number: 561704

**FESTO**



## Data sheet

| Feature                                         | Value                                                                                                                                      |
|-------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------|
| Outside diameter                                | 10 mm                                                                                                                                      |
| Bending radius relevant for flow rate           | 42 mm                                                                                                                                      |
| Inside diameter                                 | 6 mm                                                                                                                                       |
| Min. bending radius                             | 12 mm                                                                                                                                      |
| Tubing characteristics                          | Suitable for energy chains                                                                                                                 |
| Operating pressure for entire temperature range | -0.095 MPa...0.9 MPa<br>-0.95 bar...9 bar<br>-13.775 psi...130.5 psi                                                                       |
| Temperature-dependent operating pressure        | -0.095 MPa...1.6 MPa<br>-0.95 bar...16 bar<br>-13.775 psi...232 psi                                                                        |
| Information on operating pressure               | For applications with weld spatter: max. 1 MPa at 20 °C, max. 0.9 MPa at 40 °C, max. 0.7 MPa at 60 °C<br>Water: max. 0.6 MPa at max. 50 °C |
| Certification                                   | German Technical Control Board (TÜV)                                                                                                       |
| Certificate issuing authority                   | B 013277 0506 00                                                                                                                           |
| Operating medium                                | Compressed air as per ISO 8573-1:2010 [7:::]<br>Water (liquid, ice-free)                                                                   |
| Material fire test                              | UL94 V-0 (3mm)<br>UL94 V-2 (0.75mm)                                                                                                        |
| LABS (PWIS) conformity                          | VDMA24364-B2-L                                                                                                                             |
| Ambient temperature                             | -35 °C...60 °C                                                                                                                             |
| Note on ambient temperature                     | unpressurised use up to 90°C                                                                                                               |
| Product weight by length                        | 0.064 kg/m                                                                                                                                 |
| Pneumatic connection                            | For plug connection outside diameter 10 mm<br>For barbed fitting, inside diameter 6 mm                                                     |
| Color                                           | Blue                                                                                                                                       |
| Information on color                            | Deviates from the standard color due to flame protection                                                                                   |
| Shore hardness                                  | D 54 +/-3                                                                                                                                  |
| Note on materials                               | RoHS-compliant                                                                                                                             |
| Material of pneumatic tubing                    | TPE-U(PU)                                                                                                                                  |