



Electric linear slide EGSK-20-125-1P

Part number: 562760

FESTO



Data sheet

Feature	Value
Working stroke	125 mm
Size	20
Reversing backlash	20 µm
Screw diameter	6 mm
Spindle pitch	1 mm/U
Mounting position	Any
Guide	Recirculating ball bearing guide
Structural design	Electromechanical linear axis with ball screw drive
Homing	Reference switch
Spindle type	Ball screw drive
Max. acceleration	10 m/s ²
Max. speed	0.19 m/s
Repetition accuracy	±0.01 mm
Corrosion resistance class (CRC)	0 - No corrosion stress
LABS (PWIS) conformity	VDMA24364 zone III
Degree of protection	IP10
Ambient temperature	0 °C...40 °C
Fixed bearing dynamic basic load rating	1000 N
Linear guide dynamic basic load rating	2849 N
Dynamic basic load rating, ball screw drive	660 N
2nd moment of area Iy	6100 mm ⁴
2nd moment of area Iz	62000 mm ⁴
Max. driving torque	0.011 Nm
Max. force Fy	1389 N
Max. force Fz	1389 N
Max. torque Mx	18.1 Nm
Max. torque My	5.8 Nm
Max. torque Mz	5.8 Nm
Max. feed force Fx	69 N
No-load driving torque	0.005 Nm
Ball screw drive statistical basic load rating	1170 N

Feature	Value
Linear guide statistical basic load rating	6300 N
Mass moment of inertia JH per meter of stroke	0.01 kgcm ²
Mass moment of inertia JO	0.00087 kgcm ²
Feed constant	1 mm/U
Statistical fixed bearing load rating	1240 N
Reference service life	500 km
Moving mass	64 g
Slide weight	64 g
Product weight	718 g
Additional slide weight	64 g
Basic weight with 0 mm stroke	380 g
Additional weight per 10 mm stroke	27 g
Type of mounting	With internal thread and dowel pin
Material of end caps	Die-cast aluminum Coated
Profile material	High-alloy stainless steel
Note on materials	RoHS-compliant
Drive cover material	Die-cast aluminum Coated
Slide material	Steel
Spindle nut material	Steel
Spindle material	Steel