


Electric linear slide EGSK-33-300-6P

Part number: 562774

FESTO



Data sheet

Feature	Value
Working stroke	300 mm
Size	33
Reversing backlash	20 µm
Screw diameter	10 mm
Spindle pitch	6 mm/U
Mounting position	Any
Guide	Recirculating ball bearing guide
Structural design	Electromechanical linear axis with ball screw drive
Homing	Reference switch
Spindle type	Ball screw drive
Max. acceleration	20 m/s ²
Max. speed	0.47 m/s
Repetition accuracy	±0.01 mm
Corrosion resistance class (CRC)	0 - No corrosion stress
LABS (PWIS) conformity	VDMA24364 zone III
Degree of protection	IP10
Ambient temperature	0 °C...40 °C
Fixed bearing dynamic basic load rating	1790 N
Linear guide dynamic basic load rating	9207 N
Dynamic basic load rating, ball screw drive	2840 N
2nd moment of area I _y	62000 mm ⁴
2nd moment of area I _z	380000 mm ⁴
Max. driving torque	0.14 Nm
Max. force F _y	2469 N
Max. force F _z	2469 N
Max. torque M _x	50.1 Nm
Max. torque M _y	16.4 Nm
Max. torque M _z	16.4 Nm
Max. feed force F _x	150 N
No-load driving torque	0.07 Nm
Ball screw drive statistical basic load rating	4900 N

Feature	Value
Linear guide statistical basic load rating	20200 N
Mass moment of inertia JH per meter of stroke	0.0771 kgcm ²
Mass moment of inertia JO	0.0115 kgcm ²
Feed constant	6 mm/U
Statistical fixed bearing load rating	2590 N
Reference service life	3000 km
Moving mass	310 g
Slide weight	310 g
Product weight	3270 g
Additional slide weight	310 g
Basic weight with 0 mm stroke	1380 g
Additional weight per 10 mm stroke	63 g
Type of mounting	With internal thread and dowel pin
Material of end caps	Die-cast aluminum Coated
Profile material	Coated High-alloy steel
Note on materials	RoHS-compliant
Drive cover material	Die-cast aluminum Coated
Slide material	Steel
Spindle nut material	Steel
Spindle material	Steel