

Guided actuator DGRF-C-GF-32- -

Part number: 563366

FESTO



Data sheet

Feature	Value
Stroke	10 mm...400 mm
Piston diameter	32 mm
Drive unit operating mode	Yoke
Cushioning	Elastic cushioning rings/pads at both ends Self-adjusting pneumatic end-position cushioning Pneumatic cushioning, adjustable at both ends
Mounting position	Any
Guide	Sliding guide
Structural design	Guide
Position sensing	For proximity sensor
Variants	For unlubricated operation
Operating pressure	0.2 MPa...1.2 MPa 2 bar...12 bar
Mode of operation	Double-acting
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	3 - High corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
For use in the food industry	See supplementary material information
Ambient temperature	-20 °C...80 °C
Impact energy in the end positions	0.4 J
Theoretical force at 6 bar, retracting	415 N
Theoretical force at 6 bar, advancing	483 N
Torsional backlash	0.098 deg
Type of mounting	With through-hole With internal thread Optionally:
Pneumatic connection	G1/8
Note on materials	RoHS-compliant
Guide rod material	High-alloy stainless steel
Housing material	Wrought aluminum alloy
Piston rod material	High-alloy stainless steel
Material of cylinder barrel	Wrought aluminum alloy

