

Radial gripper HGRT-40-A-G2

Part number: 563913

FESTO



Data sheet

Feature	Value
Size	40
Max. interchangeability	0.2 mm
Max. gripper jaw angular play ax, ay	0.1 deg
Max. opening angle	180 deg
Rotational symmetry	0.2 mm
Pneumatic gripper repetition accuracy	0.02 mm
Number of gripper jaws	2
Mounting position	Any
Mode of operation	Double-acting
Gripper function	Radial
Gripping force backup	During closing
Structural design	Positively driven motion sequence
Position sensing	For proximity sensor For inductive proximity sensors
Operating pressure	4 bar...8 bar
Max. operating frequency of pneumatic gripper	2 Hz
Min. opening time at 6 bar	370 ms
Min. closing time at 6 bar	270 ms
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	5 °C...60 °C
Mass moment of inertia	15.26 kgcm ²
Maximum force on gripper jaw Fz, static	400 N
Maximum torque on gripper jaw, My static	17.5 Nm
Maximum torque on gripper jaw, Mz static	1.6 Nm
Relubrication interval for guidance elements	10 MioCyc
Product weight	1770 g
Type of mounting	With internal thread and centering sleeve
Pneumatic connection	G1/8
Note on materials	RoHS-compliant

Feature	Value
Housing material	Wrought aluminum alloy, smooth-anodized
Gripper jaw material	Hardened steel