



Mini slide

EGSL-BS-75-100-20P

Part number: 559340

FESTO



Data sheet

Feature	Value
Working stroke	100 mm
Size	75
Run. parallelism along Z-axis	0.04 mm
Parallelism	0.05 mm
Reversing backlash	50 µm
Screw diameter	20 mm
Spindle pitch	20 mm/U
Mounting position	Any
Guide	Ball bearing cage guide
Structural design	Electrical mini-slide Guide with ball screw drive
Motor type	Stepper motor Servo motor
Spindle type	Ball screw drive
Position sensing	For proximity sensor
Max. acceleration	25 m/s ²
Max. speed	1.3 m/s
Repetition accuracy	±0.015 mm
Duty cycle	100%
Corrosion resistance class (CRC)	0 - No corrosion stress
LABS (PWIS) conformity	VDMA24364 zone III
Noise level	65 dB(A)
Degree of protection	IP40
Ambient temperature	0 °C...60 °C
Continuous feed force	300 N
Max. driving torque	2.231 Nm
Max. force F _y	1539 N
Max. force F _z	1539 N
Max. torque M _x	67.4 Nm
Max. torque M _y	47.1 Nm
Max. torque M _z	47.1 Nm

Feature	Value
Max. radial force on actuator shaft	300 N
Max. feed force Fx	450 N
No-load driving torque	0.155 Nm
Guide value for payload, horizontal	14 kg
Guide value for payload, vertical	14 kg
Mass moment of inertia JL per kg of payload	0.1013 kgcm ²
Mass moment of inertia JO	1.0512 kgcm ²
Feed constant	20 mm/U
Maintenance interval	Life-time lubrication
Moving mass	2280 g
Product weight	5100 g
Type of mounting	With internal thread With centering sleeve With accessories
Note on materials	RoHS-compliant
Cover material	Cast aluminum Painted
Guide rail material	Roller bearing steel
Housing material	Wrought aluminum alloy Anodized
Material of yoke plate	Wrought aluminum alloy Anodized
Spindle nut material	Roller bearing steel
Spindle material	Roller bearing steel