

Parallel gripper HGPT-80-A-B-F-G1

Part number: 560238

FESTO



Data sheet

Feature	Value
Size	80
Stroke per gripper jaw	12.5 mm
Max. interchangeability	0.2 mm
Max. gripper jaw angular play ax, ay	0.1 deg
Max. gripper jaw backlash Sz	0.02 mm
Rotational symmetry	0.2 mm
Pneumatic gripper repetition accuracy	0.05 mm
Number of gripper jaws	2
Actuator system	Pneumatic
Mounting position	Any
Mode of operation	Double-acting
Gripper function	Parallel
Gripping force backup	On opening
Structural design	Inclined plane Positively driven motion sequence
Position sensing	For proximity sensor
Operating pressure	4 bar...8 bar
Operating pressure for sealing air	0 bar...0.5 bar
Max. operating frequency of pneumatic gripper	2 Hz
Min. opening time at 6 bar	180 ms
Min. closing time at 6 bar	340 ms
Max. mass per external gripper finger	1830 g
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Degree of protection	IP40
Ambient temperature	5 °C...60 °C
Mass moment of inertia	238.336 kgcm ²
Maximum force on gripper jaw Fz, static	7000 N
Maximum torque on gripper jaw, Mx static	180 Nm
Maximum torque on gripper jaw, My static	220 Nm

Feature	Value
Maximum torque on gripper jaw, Mz static	170 Nm
Relubrication interval for guidance elements	5 MioCyc
Product weight	6287 g
Type of mounting	With internal thread and centering sleeve Via through-hole and centering sleeve With through-hole and dowel pin With internal thread and dowel pin Optionally:
Sealing air pneumatic connection	M5
Pneumatic connection	G1/4
Note on materials	RoHS-compliant
Cover cap material	High-alloy stainless steel
Housing material	Aluminum, anodized
Gripper jaw material	Hardened steel