



Air solenoid valve

VUVG-L10-P53E-ZT-M7-1P3

Part number: 566485

FESTO



Data sheet

| Feature | Value |
|--|--|
| Valve function | 5/3, exhausted |
| Actuation type | Electrical |
| Valve size | 10 mm |
| Standard nominal flow rate | 300 l/min...320 l/min |
| Pneumatic working port | M7 |
| Operating voltage | 24V DC |
| Operating pressure | -0.09 MPa...1 MPa -0.9 bar...10 bar |
| Structural design | Piston gate valve |
| Reset method | Mechanical spring |
| Certification | RCM compliance mark c UL us - Recognized (OL) |
| Degree of protection | IP40 IP65 With plug socket |
| Nominal width | 3.5 mm |
| Exhaust air function | With flow control option |
| Sealing principle | Soft |
| Mounting position | Any |
| Manual override | Detenting Non-detenting Covered |
| Type of control | Pilot-controlled |
| Pilot air supply port | External |
| Lap | Indefinite overlap |
| Pilot pressure MPa | 0.3 MPa...0.8 MPa |
| Pilot pressure | 3 bar...8 bar |
| Suitability for vacuum | yes |
| Switching time off | 30 ms |
| On switching time | 11 ms |
| Changeover time | 14 ms |
| Duty cycle | 100% |
| Max. positive test pulse with 0 signal | 700 µs |

| Feature | Value |
|--|--|
| Max. negative test pulse on 1 signal | 900 µs |
| Coil characteristics | 24 V DC: 1.0 W 24 V DC: low-current phase 0.3 W, high-current phase 1.0 W |
| Permissible voltage fluctuations | +/- 10 % |
| Operating medium | Compressed air as per ISO 8573-1:2010 [7:4:4] |
| Information on operating and pilot media | Operation with oil lubrication possible (required for further use) |
| Vibration resistance | Transport application test with severity level 2 as per FN 942017-4 and EN 60068-2-6 |
| Restricted ambient and media temperature | -5 - 50 °C Without holding power reduction |
| Shock resistance | Shock test with severity level 2 as per FN 942017-5 and EN 60068-2-27 |
| Corrosion resistance class (CRC) | 2 - Moderate corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Cleanroom class | Class 5 according to ISO 14644-1 |
| Temperature of medium | -5 °C...60 °C |
| Pilot medium | Compressed air as per ISO 8573-1:2010 [7:4:4] |
| Ambient temperature | -5 °C...60 °C |
| Product weight | 55 g |
| Electrical connection | Via electrical sub-base |
| Type of mounting | On terminal strip With through-hole Optionally: |
| Pilot air port 12/14 | M3 |
| Pneumatic connection 1 | M7 |
| Pneumatic connection 2 | M7 |
| Pneumatic connection 3 | M7 |
| Pneumatic connection 4 | M7 |
| Pneumatic connection 5 | M7 |
| Note on materials | RoHS-compliant |
| Seals material | HNBR NBR |
| Housing material | Wrought aluminum alloy |