


Linear actuator DGC-25- -HD-

Part number: 567548

FESTO



Data sheet

Feature	Value
Stroke	1 mm...5000 mm
Piston diameter	25 mm
Cushioning	Pneumatic shock absorber, hard characteristic curve Pneumatic shock absorber, soft characteristic curve
Mounting position	Any
Guide	Recirculating ball bearing guide
Position sensing	For proximity sensor
Variants	Protected recirculating ball bearing guide Additional slide, standard, on left Additional slide, standard on right
Operating pressure	0.25 MPa...0.8 MPa 2.5 bar...8 bar
Mode of operation	Double-acting
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	0 - No corrosion stress
LABS (PWIS) conformity	VDMA24364 zone III
Ambient temperature	-10 °C...60 °C
Theoretical force at 6 bar, retracting	295 N
Theoretical force at 6 bar, advancing	295 N
Moving mass	2.25 kg
Moving mass at 0 mm stroke	7.51 kg
Additional weight per 10 mm stroke	0.105 kg
Type of mounting	With accessories
Note on materials	RoHS-compliant
Cover material	Wrought aluminum alloy
Seals material	NBR TPE-U(PU)