


Compressed air filter MS9-LF-G-EUM

Part number: 564106

FESTO



Data sheet

Feature	Value
Size	9
Series	MS
Mounting position	Vertical +/- 5°
Grade of filtration	40 µm
Condensate drain	Manually rotating
Structural design	Sinter filter with centrifugal separator
Degree of condensate separation	75 %
Operating pressure	0 bar...20 bar
Operating medium	Compressed air as per ISO 8573-1:2010 [:-9:-] Inert gas
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Storage temperature	-10 °C...60 °C
Air quality class at the output	Compressed air as per ISO 8573-1:2010 [7:8:4]
Temperature of medium	-10 °C...60 °C
Ambient temperature	-10 °C...60 °C
Pore size	40 µm
Product weight	2000 g
Type of mounting	Line installation With accessories Optionally:
Covering material	PA-reinforced
Material of spin disc	POM
Material of filter support	POM
Note on materials	RoHS-compliant
Material of sub-base	Die-cast aluminum
Material of mounting bracket	Die-cast aluminum
Compressed air filter material	PE
Housing material	Die-cast aluminum
Module connector material	Die-cast aluminum
Material of bowl	Wrought aluminum alloy
Shell sealing material	NBR

Feature	Value
Inspection window material	PA
Separating disc material	POM