


# Intermediate plate VABF-S4-2-S

Part number: 573200

**FESTO**



## Data sheet

| Feature                                    | Value  |
|--|--|
| Width                                      | 18 mm  |
| Based on norm                              | ISO 15407-2  |
| Mounting position                          | Any  |
| Operating pressure                         | 0.3 MPa...1 MPa<br>3 bar...10 bar                                  |
| CE marking (see declaration of conformity) | As per EU low voltage directive                                    |
| Operating medium                           | Compressed air as per ISO 8573-1:2010 [7:4:4]                      |
| Information on operating and pilot media   | Operation with oil lubrication possible (required for further use) |
| Corrosion resistance class (CRC)           | 0 - No corrosion stress  |
| LABS (PWIS) conformity                     | VDMA24364-B1/B2-L  |
| Degree of protection                       | IP65<br>NEMA 4   |
| Ambient temperature                        | -5 °C...50 °C  |
| Product weight                             | 203.5 g  |
| Vertical stacking mounting type            | On manifold sub-base<br>On individual sub-base                     |
| Pilot air port 14                          | Sub-base, size 18 mm as per ISO 15407-2                            |
| Pneumatic connection 1                     | Sub-base, size 18 mm as per ISO 15407-2                            |
| Pneumatic connection 4                     | Sub-base, size 18 mm as per ISO 15407-2                            |
| Pneumatic connection 5                     | Sub-base, size 18 mm as per ISO 15407-2                            |
| Note on materials                          | RoHS-compliant   |
| Plate material                             | Wrought aluminum alloy   |