


# Electric actuator ESBF-BS-80-400-5P

Part number: 574106

FESTO



## Data sheet

| Feature                                      | Value                                  |
|----------------------------------------------|----------------------------------------|
| Working stroke                               | 400 mm                                 |
| Size                                         | 80                                     |
| Stroke                                       | 400 mm                                 |
| Piston rod thread                            | M20x1.5                                |
| Reversing backlash                           | 30 µm                                  |
| Screw diameter                               | 32 mm                                  |
| Spindle pitch                                | 5 mm/U                                 |
| Max. angle of rotation of the piston rod +/- | 0.5 deg                                |
| Based on norm                                | ISO 15552                              |
| Mounting position                            | Any                                    |
| Piston rod end                               | External thread                        |
| Motor type                                   | Servo motor                            |
| Position sensing                             | For proximity sensor                   |
| Structural design                            | Electric actuator with ball screw      |
| Spindle type                                 | Ball screw                             |
| Protection against torsion/guide             | With plain-bearing guide               |
| Max. acceleration                            | 5 m/s <sup>2</sup>                     |
| Max. rotational speed                        | 2530 rpm                               |
| Max. speed                                   | 0.25 m/s                               |
| Repetition accuracy                          | ±0.01 mm                               |
| Duty cycle                                   | 100%                                   |
| Corrosion resistance class (CRC)             | 2 - Moderate corrosion stress          |
| LABS (PWIS) conformity                       | VDMA24364 zone III                     |
| Storage temperature                          | -20 °C...60 °C                         |
| For use in the food industry                 | See supplementary material information |
| Relative air humidity                        | 0 - 95 %                               |
| Degree of protection                         | IP40                                   |
| Ambient temperature                          | 0 °C...60 °C                           |
| Max. driving torque                          | 11.9 Nm                                |
| Max. radial force on actuator shaft          | 1100 N                                 |
| Max. feed force Fx                           | 12000 N                                |

| Feature                                       | Value                                   |
|-----------------------------------------------|-----------------------------------------|
| No-load driving torque                        | 0.5 Nm                                  |
| Guide value for payload, horizontal           | 1200 kg                                 |
| Guide value for payload, vertical             | 1200 kg                                 |
| Mass moment of inertia JH per meter of stroke | 7.699 kgcm <sup>2</sup>                 |
| Mass moment of inertia JL per kg of payload   | 0.00633 kgcm <sup>2</sup>               |
| Mass moment of inertia JO                     | 1.5297 kgcm <sup>2</sup>                |
| Maintenance interval                          | Life-time lubrication                   |
| Moving mass at 0 mm stroke                    | 5300 g                                  |
| Additional moving mass per 10 mm stroke       | 103 g                                   |
| Basic weight with 0 mm stroke                 | 7393 g                                  |
| Additional weight per 10 mm stroke            | 155 g                                   |
| Type of mounting                              | With internal thread<br>or accessory    |
| Interface code, actuator                      | D80                                     |
| Note on materials                             | RoHS-compliant                          |
| Cover material                                | Die-cast aluminum, coated               |
| Piston rod material                           | High-alloy stainless steel              |
| Material of screws                            | Steel, galvanized                       |
| Spindle nut material                          | Roller bearing steel                    |
| Spindle material                              | Roller bearing steel                    |
| Material of cylinder barrel                   | Wrought aluminum alloy, smooth-anodized |