


Proximity sensor

SMT-8M-A-PO-24V-E-7,5-OE

Part number: 574340

FESTO



Data sheet

| Feature | Value |
|--|---|
| Design | for T-slot |
| Based on norm | EN 60947-5-2 |
| Certification | RCM compliance mark c UL us - Listed (OL) |
| CE marking (see declaration of conformity) | As per EU EMC directive As per EU RoHS directive |
| UKCA marking (see declaration of conformity) | To UK instructions for EMC To UK RoHS instructions |
| Certificate issuing authority | UL E232949 |
| Special features | Oil-resistant |
| Note on materials | RoHS-compliant Halogen-free |
| Application note | https://www.festo.com/Drive-Sensor-Overview |
| Measured variable | Position |
| Measuring principle | Magneto-resistive |
| Ambient temperature | -40 °C...85 °C |
| Repetition accuracy | 0.2 mm |
| Switching output | PNP |
| Switching element function | N/C contact |
| On time | 1.3 ms |
| Switch-off time | 7.3 ms |
| Max. switching frequency | 130 Hz |
| Max. output current | 100 mA |
| Max. output current in mounting kits | 100 mA |
| Max. switching capacity DC | 2.8 W |
| Max. switching capacity DC in mounting kits | 2.8 W |
| Voltage drop | 1.5 V |
| Short-circuit protection | yes |
| Overload protection | Available |
| Rated operating voltage DC | 24 V |
| DC operating voltage range | 5 V...30 V |
| Reverse polarity protection | for all electrical connections |

| Feature | Value |
|--|---|
| Electrical connection 1, connection type | Cable |
| Electrical connection 1, connection technology | Open end |
| Electrical connection 1, number of pins/wires | 3 |
| Connection outlet orientation | Longitudinal |
| Connector cable test conditions | Test conditions on request Torsion resistance: > 300,000 cycles, $\pm 270^\circ/0.1$ m Flexural strength: > 50000 cycles, bending radius 5 mm Energy chain > 5 million cycles, bending radius 28 mm |
| Cable length | 7.5 m |
| Cable characteristic | Suitable for energy chains/robot applications |
| Color cable sheath | Gray |
| Material of cable sheath | TPE-U(PUR) |
| Insulating sheath material | PP |
| Wire ends | Cable end sleeve |
| Type of mounting | Screwed tightly Can be inserted in slot from above |
| Max. tightening torque | 0.6 Nm |
| Mounting position | Any |
| Product weight | 85.1 g |
| Housing colour | Black |
| Housing material | PA-reinforced High-alloy stainless steel |
| Switching status indication | LED yellow |
| Function reserve indication | LED orange |
| Ambient temperature with flexible cable installation | -20 °C...85 °C |
| Degree of protection | IP65 IP68 IP69K |
| LABS (PWIS) conformity | VDMA24364-B2-L |
| Suitability for the production of Li-ion batteries | Product corresponds to Festo's internal product definition for use in battery production: Metals with more than 1% by mass of copper, zinc or nickel are excluded from use. The exceptions are nickel in steel, chemically nickel-plated surfaces, circuit boards, cables, electrical plug connectors and coils |
| Cleanroom class | Statically installed element, no meaningful evaluation possible according to ISO 14644-1 |