


Electric actuator ESBF-BS-80-300-32P

Part number: 574113

FESTO



Data sheet

Feature	Value
Working stroke	300 mm
Size	80
Stroke	300 mm
Piston rod thread	M20x1.5
Reversing backlash	40 µm
Screw diameter	32 mm
Spindle pitch	32 mm/U
Max. angle of rotation of the piston rod +/-	0.5 deg
Based on norm	ISO 15552
Mounting position	Any
Piston rod end	External thread
Motor type	Servo motor
Position sensing	For proximity sensor
Structural design	Electric actuator with ball screw
Spindle type	Ball screw
Protection against torsion/guide	With plain-bearing guide
Max. acceleration	25 m/s ²
Max. rotational speed	2515 rpm
Max. speed	1.33 m/s
Repetition accuracy	±0.01 mm
Duty cycle	100%
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364 zone III
Storage temperature	-20 °C...60 °C
For use in the food industry	See supplementary material information
Relative air humidity	0 - 95 %
Degree of protection	IP40
Ambient temperature	0 °C...60 °C
Max. driving torque	56.6 Nm
Max. radial force on actuator shaft	1100 N
Max. feed force Fx	10002 N

Feature	Value
No-load driving torque	0.65 Nm
Guide value for payload, horizontal	1000 kg
Guide value for payload, vertical	1000 kg
Mass moment of inertia JH per meter of stroke	8.277 kgcm ²
Mass moment of inertia JL per kg of payload	0.25938 kgcm ²
Mass moment of inertia JO	2.1197 kgcm ²
Maintenance interval	Life-time lubrication
Moving mass at 0 mm stroke	5300 g
Additional moving mass per 10 mm stroke	103 g
Basic weight with 0 mm stroke	7393 g
Additional weight per 10 mm stroke	155 g
Type of mounting	With internal thread or accessory
Interface code, actuator	D80
Note on materials	RoHS-compliant
Cover material	Die-cast aluminum, coated
Piston rod material	High-alloy stainless steel
Material of screws	Steel, galvanized
Spindle nut material	Roller bearing steel
Spindle material	Roller bearing steel
Material of cylinder barrel	Wrought aluminum alloy, smooth-anodized