

# Input/output module CPX-2ZE2DA

Part number: 576046

FESTO



## Data sheet

Feature	Value
Dimensions W x L x H	(incl. interlinking block and connection system) 50 mm x 107 mm x 50 mm
Width dimension	50 mm
Product weight	130 g
Ambient temperature	-5 °C...50 °C
Storage temperature	-20 °C...70 °C
Degree of protection	IP65 IP67
Corrosion resistance class (CRC)	1 - Low corrosion stress (when installed)
Max. cable length	30 m
LABS (PWIS) conformity	VDMA24364-B2-L
Certification	UL - Recognized (OL)
Note on materials	RoHS-compliant
Housing material	Polymer
LED indicators	1 group diagnostics 10 channel status 2 module diagnostics 2 channel diagnostics
Diagnostics	Operating-mode-dependent diagnostics
No. of outputs	2
Parameterization	On/off delay Frequency output Speed measurement Pulse output Pulse train Rotational speed measurement Frequency measurement Period duration measurement Motor operating mode Position determination Pulse width modulation One-off counting Infinite counting Periodic counting
DC operating voltage range	18 V...30 V
Nominal operating voltage DC	24 V

Feature	Value
Intrinsic current consumption at nominal operating voltage	Typ. 35 mA
No. of inputs	2
Input characteristics	As per IEC 1131-2, type 02
Switching level	Signal 0: $\leq 5$ V Signal 1: $\geq 11$ V
Input switching logic	PNP (positive switching)
Input debounce time	0.1 $\mu$ s (0.2 $\mu$ s, 0.4 $\mu$ s, 0.8 $\mu$ s, 1 $\mu$ s, 2 $\mu$ s, 4 $\mu$ s, 8 $\mu$ s, 10 $\mu$ s, 50 $\mu$ s, 100 $\mu$ s, 500 $\mu$ s, 1ms, 3ms, 10ms, 20ms, parameterizable)
Max. residual current of inputs per module	2 A
Characteristic curve outputs	IEC1131-T2
Switching logic at outputs	NPN (negative switching) PNP (positive switching) Push-pull driver
Max. residual current of outputs per module	10 A
Max. power supply per channel	5 A adjustable (20 W lamp load)
Electrical isolation between channels	no
Electrical isolation between channel and internal bus	Outputs - yes, when using an intermediate supply
Fuse protection (short circuit)	Internal electronic fuse per channel