


Encoder cable

NEBM-M12G8-E-15-N-S1G15

Part number: 8003764

FESTO



Data sheet

Feature	Value
Cable designation	Without label holder
Electrical connection 1, function	Field device end
Electrical connection 1, design	Round
Electrical connection 1, connection type	Socket
Electrical connection 1, cable outlet	Straight
Electrical connection 1, connection technology	M12x1 A-coded as per EN 61076-2-101
Electrical connection 1, number of pins/wires	8
Electrical connection 1, occupied pins/wires	8
Electrical connection 2, function	Control side
Electrical connection 2, design	Rectangular
Electrical connection 2, connection type	Plug
Electrical connection 2, cable outlet	Straight
Electrical connection 2, connection technology	Sub-D
Electrical connection 2, number of pins/wires	15
Electrical connection 2, occupied pins/wires	8
DC operating voltage range	0 V...30 V
Nominal operating voltage DC	24 V
Operating voltage range AC	0 V...30 V
Nominal operating voltage AC	24 V
Shield	yes
Cable length	15 m
Cable characteristic	Suitable for energy chains
Bending radius, flexible cable installation	68 mm
Cable diameter	6.8 mm
Cable design	4 x 2 x 0.14 mm ²
Nominal conductor cross section	0.14 mm ²
Degree of protection	IP65
Note on degree of protection	IP30 for Sub-D plug In mounted state
Ambient temperature	-40 °C...80 °C

Feature	Value
Ambient temperature with flexible cable installation	-5 °C...80 °C
CE marking (see declaration of conformity)	As per EU RoHS directive
UKCA marking (see declaration of conformity)	To UK RoHS instructions
LABS (PWIS) conformity	VDMA24364-B2-L
Note on materials	RoHS-compliant
Corrosion resistance class (CRC)	0 - No corrosion stress
Material of cable sheath	TPE-U(PUR)
Color cable sheath	Gray