


Individual subbase VABS-S1-2S-N12

Part number: 8032645

FESTO



Data sheet

Feature	Value
Width	58 mm
Based on norm	ISO 5599-1
Operating pressure	0 MPa...1.6 MPa 0 bar...16 bar
Pilot pressure MPa	0 MPa...1 MPa
Pilot pressure	0 bar...10 bar
Suitability for vacuum	yes
CE marking (see declaration of conformity)	As per EU low voltage directive
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	0 - No corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Storage temperature	-20 °C...60 °C
Temperature of medium	-10 °C...60 °C
Pilot medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Ambient temperature	-10 °C...60 °C
Product weight	380 g
Type of mounting	with through-hole for M6 screw
Pilot air port 12/14	1/8 NPT
Pneumatic connection 1	1/2 NPT
Pneumatic connection 2	1/2 NPT
Pneumatic connection 3	1/2 NPT
Pneumatic connection 4	1/2 NPT
Pneumatic connection 5	1/2 NPT
Note on materials	RoHS-compliant
Material of sub-base	Die-cast aluminum