

Belt driven linear actuator ELGA-TB-KF-150- -

Part number: 8024917

FESTO



Data sheet

Feature	Value
Drive pinion effective diameter	73.85 mm
Working stroke	50 mm...7000 mm
Size	150
Toothed belt pitch	8 mm
Mounting position	Any
Guide	Recirculating ball bearing guide
Structural design	Electromechanical linear axis with toothed belt
Motor type	Stepper motor Servo motor
Measuring principle of linear potentiometer	Incremental
Max. acceleration	50 m/s ²
Max. speed	5 m/s
Repetition accuracy	±0.08 mm
Duty cycle	100%
LABS (PWIS) conformity	VDMA24364 zone III
Degree of protection	IP40
Ambient temperature	-10 °C...60 °C
Max. force F _y	11000 N
Max. force F _z	11000 N
Max. force F _y total axis	11000 N
Max. force F _z total axis	11000 N
F _y with theoretical service life of 100 km (from a guide perspective only)	40480 N
F _z with theoretical service life of 100 km (from a guide perspective only)	40480 N
Max. torque M _x	167 Nm
Max. torque M _y	1150 Nm
Max. torque M _z	1150 Nm
Max. moment M _x total axis	167 Nm
Max. moment M _y total axis	1150 Nm
Max. moment M _z total axis	1150 Nm
M _x with theoretical service life of 100 km (from a guide perspective only)	615 Nm

Feature	Value
My with theoretical service life of 100 km (from a guide perspective only)	4232 Nm
Mz with theoretical service life of 100 km (from a guide perspective only)	4232 Nm
Distance between slide surface and guide center	86 mm
Max. feed force Fx	2000 N
Feed constant	232 mm/U
Reference service life	5000 km
Slide weight	7.24 kg
Additional slide weight	5.84 kg
Dynamic deflection (load moved)	0.05% of axis length, maximum 0.5 mm
Static deflection (load at standstill)	0.1 % of axis length
Profile material	Wrought aluminum alloy, anodized
Note on materials	RoHS-compliant
Cover strip material	Stainless steel strip
Drive cover material	Wrought aluminum alloy, anodized
Slide carriage material	Tempered steel
Guide rail material	Tempered steel Corroprotect coated
Belt pulley material	High-alloy stainless steel
Slide material	Wrought aluminum alloy, anodized
Toothed belt clamping component material	Cast stainless steel
Toothed belt material	Polyurethane with steel cord and nylon cover Polyurethane with steel cord Polychloroprene oder Nitrilkautschuk (NBR) mit Glascord und Nylonüberzug