

Linear gantry
EXCT-15- -
Part number: 8026575

FESTO



Data sheet

Feature	Value
Size	15
Mounting position	Vertical
Structural design	Linear gantry
Operating pressure	-0.95 bar...8 bar
Max. acceleration	50 m/s ²
Max. speed	4.8 m/s
Repetition accuracy	±0.1 mm
Duty cycle	100%
LABS (PWIS) conformity	VDMA24364 zone III
Storage temperature	-10 °C...60 °C
Relative air humidity	0 - 90 %
Noise level	70 dB(A)
Degree of protection	IP40
Ambient temperature	10 °C...40 °C
Max. process force in Z direction	100 N
Rated load with maximum dynamic response	1.5 kg
Type of mounting	With mounting kit With slot nuts
Note on materials	RoHS-compliant