



**Distributor**  
**NEDY-L2R1-V1-Z4W2Z-U-0.3L-M8G4-5R**  
Part number: 8035790

**FESTO**



**Data sheet**

Feature	Value
Based on norm	EN 61076-2-104
Certification	RCM compliance mark
Structural design	Y-distributor with cables at both ends
Distributor type	2 to 1
Signal status display	LED yellow
Additional functions	Holding current reduction
Cable designation	With label holder
Type of mounting	With through-hole for M2 screw With accessories
Product weight	131 g
Electrical connection 1, function	Control side
Electrical connection 1, design	Round
Electrical connection 1, connection type	Plug
Electrical connection 1, cable outlet	Straight
Electrical connection 1, connection technology	M8x1 A-coded as per EN 61076-2-104
Electrical connection 1, number of pins/wires	4
Electrical connection 1, occupied pins/wires	3
Electrical connection 2, function	Field device end
Electrical connection 2, design	Rectangular
Electrical connection 2, connection type	2x socket
Electrical connection 2, cable outlet	Angled
Electrical connection 2, connection technology	Connection diagram ZC, metric screw
Electrical connection 2, number of pins/wires	2
Electrical connection 2, occupied pins/wires	2
DC operating voltage range	20.4 V...27.6 V
Current rating at 40° C	1 A
Surge resistance	0.8 kV
Cable length 1	5 m
Cable length 2	0.3 m

Feature	Value
Cable characteristic	Suitable for energy chains/robot applications
Information on cable characteristics	Standard for field device side
Connector cable test conditions	Flexural strength: as per Festo standard Test conditions on request Torsionsfestigkeit: > 300 000 Zyklen, ±270°/0,1 m Energy chain > 5 million cycles, bending radius 28 mm
Note on connector cable test conditions	For standard cable characteristics: energy chain: 1.5 million cycles, bending radius 75 mm, flexural strength: as per Festo standard, test conditions on request
Bending radius 1, flexible cable installation	39 mm
Bending radius 2, flexible cable installation	30 mm
Cable diameter 1	3.8 mm
Cable diameter 2	2.9 mm
Nominal conductor cross section	0.25 mm <sup>2</sup>
Degree of protection	IP65
Ambient temperature	-10 °C...50 °C
Note on ambient temperature	-10 - 40 °C when mounted via through-hole
Ambient temperature with flexible cable installation	-5 °C...50 °C
Storage temperature	-10 °C...50 °C
CE marking (see declaration of conformity)	As per EU EMC directive As per EU RoHS directive
UKCA marking (see declaration of conformity)	To UK instructions for EMC To UK RoHS instructions
LABS (PWIS) conformity	VDMA24364-B2-L
Note on materials	RoHS-compliant
Contamination level	3
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
Material of cable sheath	TPE-U(PUR)
Color cable sheath	Gray
Housing material	PA TPE-U(PUR)
Housing colour	Black
Seals material	NBR TPE-O
Material of pin contacts	Copper alloy, gold-plated Copper alloy, tin-plated
Threaded sleeve material	Brass, nickel-plated