


Cantilever linear actuator ELCC-TB-KF-70- -

Part number: 8060572

FESTO



Data sheet

Feature	Value
Drive pinion effective diameter	30.558 mm
Working stroke	50 mm...1500 mm
Size	70
Stroke reserve	0 mm...1500 mm
Toothed belt pitch	3 mm
Mounting position	Any
Guide	Recirculating ball bearing guide
Structural design	Electromechanical cantilever axis
Max. acceleration	50 m/s ²
Max. speed	5 m/s
Repetition accuracy	±0.05 mm
Corrosion resistance class (CRC)	0 - No corrosion stress
LABS (PWIS) conformity	VDMA24364 zone III
Degree of protection	IP20
Ambient temperature	-10 °C...60 °C
2nd moment of area Iy	959740 mm ⁴
2nd moment of area Iz	928740 mm ⁴
Max. driving torque	10.4 Nm
Max. force Fy	9680 N
Max. force Fz	9406 N
Max. torque Mx	104 Nm
Max. torque My	826 Nm
Max. torque Mz	797 Nm
Max. feed force Fx	600 N
Mass moment of inertia JH per meter of stroke	14.7 kgcm ²
Mass moment of inertia JL per kg of payload	2.3 kgcm ²
Mass moment of inertia JO	10.6 kgcm ²
Feed constant	96 mm/U
Reference service life	5000 km
Lubrication interval, distance dependent	1000 km
Moved mass at 0 mm stroke with second drive head	5516 g

Feature	Value
Moving mass at 0 mm stroke	3210 g
Additional moving mass per 10 mm stroke	63 g
Additional slide weight	2010 g
Basic weight with 0 mm stroke	7960 g
Additional weight per 10 mm stroke	63 g
Basic weight at 0 mm stroke with second drive head	12275 g
Material of end caps	Wrought aluminum alloy, anodized
Profile material	Wrought aluminum alloy, anodized
Note on materials	RoHS-compliant
Drive head material	Wrought aluminum alloy, anodized
Guide rail material	Rolled steel, Corrotect coated
Housing material	High-alloy stainless steel
Slide material	Cast aluminum, anodized
Toothed belt clamping component material	Wrought aluminum alloy, anodized
Toothed belt material	Polychloroprene with glass cord and nylon coating Polyurethane with steel cord and textile coating Polyurethane with steel cord