


Connecting cable

NEBB-M8W3-P-2.5-LE3

Part number: 8066664

FESTO



Data sheet

| Feature | Value |
|--|---|
| Conforms to standard | Wire colors and connection numbers as per EN 60947-5-2 EN 61076-2-104 |
| Explosion prevention and protection | Observe the information on the certificate Zone 2 (ATEX) Zone 22 (ATEX) |
| Cable designation | With label holder |
| Electrical connection 1, function | Field device end |
| Electrical connection 1, design | Round |
| Electrical connection 1, connection type | Socket |
| Electrical connection 1, cable outlet | Angled |
| Electrical connection 1, connection technology | M8x1 A-coded as per EN 61076-2-104 |
| Electrical connection 1, number of pins/wires | 3 |
| Electrical connection 1, occupied pins/wires | 3 |
| Electrical connection 1, type of mounting | Screw-type lock with AF 9 |
| Electrical connection 2, function | Control side |
| Electrical connection 2, connection type | Cable |
| Electrical connection 2, connection technology | Open end |
| Electrical connection 2, number of pins/wires | 3 |
| Electrical connection 2, occupied pins/wires | 3 |
| DC operating voltage range | 0 V...60 V |
| Operating voltage range AC | 0 V...60 V |
| Current rating at 40° C | 4 A |
| Surge resistance | 1.5 kV |
| Cable length | 2.5 m |
| Cable characteristic | for static applications |
| Connector cable test conditions | Test conditions on request |
| Bending radius, fixed cable installation | 12 mm |
| Cable diameter | 3.8 mm |
| Cable design | 3 x 0.25 mm ² |
| Nominal conductor cross section | 0.25 mm ² |

| Feature | Value |
|--|--|
| Wire ends | Stripped Cut off bluntly |
| Degree of protection | IP65 IP68 IP69K |
| Note on degree of protection | In mounted state |
| Ambient temperature | -25 °C...70 °C |
| CE marking (see declaration of conformity) | As per EU low voltage directive As per EU RoHS directive |
| UKCA marking (see declaration of conformity) | To UK RoHS instructions To UK instructions for electrical equipment |
| LABS (PWIS) conformity | VDMA24364-B2-L |
| Cleanroom class | Class 4 according to ISO 14644-1 |
| Note on materials | RoHS-compliant |
| Contamination level | 3 |
| Corrosion resistance class (CRC) | 2 - Moderate corrosion stress |
| Material of cable sheath | PVC |
| Color cable sheath | Gray |
| Housing material | TPE-U(PU) |
| Housing colour | Black |
| Material of screw-type lock | Brass, nickel-plated |
| Seals material | NBR |
| Material of pin contacts | Copper alloy, gold-plated |
| Insulating sheath material | PVC |