

Proportional pressure control valve VEAB-B-26-D7-F-V1-1R1

Part number: 8046267

FESTO



Data sheet

| Feature | Value |
|--------------------------------|--|
| Valve function | 3-way proportional pressure control valve |
| Type of control | Direct |
| Reset method | Mechanical spring |
| Actuation type | Electrical |
| Mounting position | Any |
| Sealing principle | Soft |
| Total leakage | 1 l/h |
| Ambient temperature | 0 °C...50 °C |
| Temperature of medium | 5 °C...50 °C |
| Storage temperature | -20 °C...70 °C |
| Dimensions W x L x H | 18 mm x 67 mm x 66 mm |
| Pneumatic connection 1 | Flange |
| Pneumatic connection 2 | Flange |
| Pneumatic connection 3 | Flange |
| Seals material | NBR |
| Type of mounting | With through-hole With accessories Optionally: |
| Inlet pressure 1 MPa | 0 MPa...0.3 MPa |
| Inlet pressure 1 | 0 bar...3 bar |
| Inlet pressure 1 psi | 0 psi...43.5 psi |
| Output pressure 2 | 0.5 kPa...100 kPa 0.0725 psi...14.5 psi |
| Outlet pressure 2 | 0.005 bar...1 bar |
| Standard nominal flow rate | 13 l/min |
| Standard nominal flow rate 2-3 | 12 l/min |
| Linearity | 0.5 %FS |
| Reproducibility | 0.4 %FS |
| Hysteresis | 0.25 %FS |
| Temperature coefficient | 0.05 %/K |
| Overall accuracy | 0.75 %FS |
| Product weight | 70 g |

| Feature | Value |
|--|---|
| Operating medium | Compressed air as per ISO 8573-1:2010 [7:4:4] Inert gas |
| Information on operating and pilot media | Operation with oil lubrication not possible |
| Degree of protection | IP65 |
| Certification | RCM compliance mark |
| KC characters | KC EMC |
| CE marking (see declaration of conformity) | As per EU EMC directive As per EU RoHS directive |
| UKCA marking (see declaration of conformity) | To UK instructions for EMC To UK RoHS instructions |
| Note on materials | RoHS-compliant |
| LABS (PWIS) conformity | VDMA24364 zone III |
| Corrosion resistance class (CRC) | 2 - Moderate corrosion stress |
| DC operating voltage range | 19 V...29 V |
| Nominal operating voltage DC | 24 V |
| Residual ripple | 10 % |
| Reference value | 0 - 10 V |
| Analog output signal range | 0 - 10 V |
| Precision analog output in ± %FS | 2 %FS |
| Max. electrical power consumption | 1 W |
| Reverse polarity protection | for all electrical connections |
| Short-circuit protection | For all electrical connections |
| Safety instructions | VEAA/VEAB safety position: if the electrical power supply is lost, the outlet pressure is maintained in uncontrolled form, it may increase or fall – pneumatic valve blocked. |
| Display type | LED |
| Electrical connection | 4-pin M8x1 Plug as per EN 60947-5-2 |
| Housing material | PA-reinforced |