

Compact air cylinder ADN-S-20-40-I-P-A

Part number: 8076328

FESTO



Data sheet

| Feature | Value |
|--|--|
| Stroke | 40 mm |
| Piston diameter | 20 mm |
| Cushioning | Elastic cushioning rings/pads at both ends |
| Mounting position | Any |
| Mode of operation | Double-acting |
| Piston rod end | Internal thread |
| Structural design | Piston Piston rod |
| Position sensing | For proximity sensor |
| Variants | Piston rod at one end |
| Operating pressure | 0.06 MPa...1 MPa 0.6 bar...10 bar |
| Operating medium | Compressed air as per ISO 8573-1:2010 [7:4:4] |
| Information on operating and pilot media | Operation with oil lubrication possible (required for further use) |
| Corrosion resistance class (CRC) | 1 - Low corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B2-L |
| Cleanroom class | Class 6 according to ISO 14644-1 |
| Ambient temperature | 0 °C...60 °C |
| Impact energy in the end positions | 0.2 J |
| Theoretical force at 6 bar, retracting | 141 N |
| Theoretical force at 6 bar, advancing | 188 N |
| Moving mass at 0 mm stroke | 18 g |
| Additional moving mass per 10 mm stroke | 6 g |
| Basic weight with 0 mm stroke | 65 g |
| Additional weight per 10 mm stroke | 26 g |
| Type of mounting | With through-hole With internal thread With accessories Optionally: |
| Pneumatic connection | M5 |
| Note on materials | RoHS-compliant |
| Cover material | Wrought aluminum alloy, anodized |

| Feature | Value |
|---------------------------|----------------------------------|
| Material of dynamic seals | NBR TPE-U(PU) |
| Housing material | Wrought aluminum alloy, anodized |
| Piston rod material | High-alloy stainless steel |