


Position transmitter SDAP-MHS-M100-1L-A-E-0.3-M8

Part number: 8050121

FESTO



Data sheet

Feature	Value
Design	for T-slot
Certification	RCM compliance mark c UL us - Listed (OL)
CE marking (see declaration of conformity)	As per EU EMC directive As per EU RoHS directive
UKCA marking (see declaration of conformity)	To UK instructions for EMC To UK RoHS instructions
Note on materials	RoHS-compliant Halogen-free
Measured variable	Position
Measuring principle	Magnetic Hall
Sensing range	0 mm...100 mm
Ambient temperature	-25 °C...70 °C
Typical sampling interval	1 ms
Max. travel speed	3 m/s
Displacement resolution	0.05 mm
Analog output	4 - 20 mA
Sensitivity	0.16 mA/mm
Typical linearity error	±0.25 mm
Max. load resistance of current output	500 Ohm
Short-circuit protection	yes
Overload protection	Available
DC operating voltage range	15 V...30 V
Residual ripple	10 %
Reverse polarity protection	for all electrical connections
Electrical connection 1, connection type	Cable with plug
Electrical connection 1, connection technology	M8x1 A-coded as per EN 61076-2-104
Electrical connection 1, number of pins/wires	4
Electrical connection 1, type of mounting	Screw-type lock
Connection outlet orientation	Longitudinal
Material of pin contacts	Copper alloy, gold-plated

Feature	Value
Connector cable test conditions	Flexural strength: as per Festo standard Torsion resistance: > 300,000 cycles, $\pm 270^\circ/0.1$ m Energy chain > 5 million cycles, bending radius 28 mm
Cable length	0.3 m
Cable characteristic	Suitable for energy chains/robot applications
Color cable sheath	Gray
Material of cable sheath	TPE-U(PUR)
Type of mounting	Screwed tightly Can be inserted in slot from above
Mounting position	Any
Product weight	26 g
Housing material	Brass, nickel-plated PA-reinforced Polyester High-alloy stainless steel
Material of union nut	Brass, nickel-plated
Film material	Polyester
Ready status indication	LED green
Status indicator	LED red
Ambient temperature with flexible cable installation	-20 °C...70 °C
Degree of protection	IP65 IP68
LABS (PWIS) conformity	VDMA24364-B2-L
Suitability for the production of Li-ion batteries	Product corresponds to Festo's internal product definition for use in battery production: Metals with more than 1% by mass of copper, zinc or nickel are excluded from use. The exceptions are nickel in steel, chemically nickel-plated surfaces, circuit boards, cables, electrical plug connectors and coils
Cleanroom class	Class 4 according to ISO 14644-1