

Cantilever linear actuator ELCC-TB-KF-110- -

Part number: 8060574

FESTO



Data sheet

Feature	Value
Drive pinion effective diameter	68.755 mm
Working stroke	50 mm...2000 mm
Size	110
Stroke reserve	0 mm...2000 mm
Toothed belt pitch	8 mm
Mounting position	Any
Guide	Recirculating ball bearing guide
Structural design	Electromechanical cantilever axis
Max. acceleration	30 m/s ²
Max. speed	5 m/s
Repetition accuracy	±0.05 mm
Corrosion resistance class (CRC)	0 - No corrosion stress
LABS (PWIS) conformity	VDMA24364 zone III
Degree of protection	IP20
Ambient temperature	-10 °C...60 °C
2nd moment of area Iy	6830570 mm ⁴
2nd moment of area Iz	4925970 mm ⁴
Max. driving torque	90 Nm
Max. force Fy	20596 N
Max. force Fz	20022 N
Max. torque Mx	317 Nm
Max. torque My	2368 Nm
Max. torque Mz	2286 Nm
Max. feed force Fx	2500 N
Mass moment of inertia JH per meter of stroke	174.9 kgcm ²
Mass moment of inertia JL per kg of payload	11.8 kgcm ²
Mass moment of inertia JO	157.1 kgcm ²
Feed constant	216 mm/U
Reference service life	5000 km
Lubrication interval, distance dependent	1000 km
Moved mass at 0 mm stroke with second drive head	16953 g

Feature	Value
Moving mass at 0 mm stroke	10017 g
Additional moving mass per 10 mm stroke	148 g
Additional slide weight	4777 g
Basic weight with 0 mm stroke	27299 g
Additional weight per 10 mm stroke	148 g
Basic weight at 0 mm stroke with second drive head	39012 g
Material of end caps	Wrought aluminum alloy, anodized
Profile material	Wrought aluminum alloy, anodized
Note on materials	RoHS-compliant
Drive head material	Wrought aluminum alloy, anodized
Guide rail material	Rolled steel, Corrotect coated
Housing material	High-alloy stainless steel
Slide material	Cast aluminum, anodized
Toothed belt clamping component material	Wrought aluminum alloy, anodized
Toothed belt material	Polychloroprene with glass cord and nylon coating