


Axial kit
EAMM-A-L95-120GA
Part number: 8063529

FESTO



Data sheet

Feature	Value
Nominal length	65.4 mm
Mounting position	Any
Max. rotational speed	4500 rpm
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-25 °C...60 °C
Relative air humidity	0 - 95 %
Degree of protection	IP40
Ambient temperature	-10 °C...60 °C
Mass moment of inertia	374 kgmm ²
Transferable torque	120 Nm
Product weight	2676 g
Interface code, actuator	L95
Interface code, motor in	120GA
Note on materials	RoHS-compliant